

**Terminal block for pluggable modules; orange separator plate;
with 2-conductor terminal blocks; 22 mm wide**

Item No.: 280-638



Terminal block for pluggable modules; orange separator plate; with 2-conductor terminal blocks; 22 mm wide

Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	280-638
EAN	4044918538794
Content	1
Order amount	1
Customer item number	

Notes

Technical data

Miscellaneous

Total number of connection points	2
Total number of potentials	2
Color	gray
Pollution degree (1)	3
Rated voltage EN (1) [V]	400 [V]
Rated surge voltage (1) [kV]	6 [kV]
Nominal current [A]	10 [A]
Connection technology (1)	CAGE CLAMP®
Cross section from (1) [mm²]	0.08 [mm²]

Printview: Terminal block for pluggable modules; orange separator plate; with 2-conductor terminal blocks; 22 mm wide - Item No.: 280-638

Technical data	
<i>Cross section up to (1) [mm²]</i>	<i>2.5 [mm²]</i>
<i>Cross section from (1) [AWG]</i>	<i>28 [AWG]</i>
<i>Cross section up to (1) [AWG]</i>	<i>14 [AWG]</i>
<i>Stripped length from (1) [mm]</i>	<i>8 [mm]</i>
<i>Stripped length up to (1) [mm]</i>	<i>9 [mm]</i>
<i>Stripped length (1) [in]</i>	<i>0.33 [in]</i>
<i>Type of wiring</i>	<i>Front-entry wiring</i>
<i>Fire load [MJ]</i>	<i>0.431 [MJ]</i>
<i>Weight [g]</i>	<i>20.875 [g]</i>
<i>Width [mm]</i>	<i>22 [mm]</i>
<i>Width [in]</i>	<i>0.866 [in]</i>
<i>Height [mm]</i>	<i>28 [mm]</i>
<i>Height [in]</i>	<i>1.102 [in]</i>
<i>Length [mm]</i>	<i>50 [mm]</i>
<i>Length [in]</i>	<i>1.969 [in]</i>
<i>Type of mounting</i>	<i>DIN 35 rail</i>

Approbation					
Item No.	Registration	Registration no.	Voltage [V]	Current [A]	Cross section [mm ² , AWG]
280-638	BV	07436/C0			0,08-2,5

Accessories

Accessories

Carrier rail

Item no.	Description	Pack. unit (Sub Pack)
210-112	Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to en 60715; "Hole width 25 mm	1
210-113	Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; according to en 60715	1
210-114	Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; according to en 60715	1
210-115	Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to en 60715; "Hole width 18 mm	1
210-118	Steel carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to en 60715	1
210-196	Aluminum carrier rail; 35 x 8.2 mm; 1.6 mm thick; 2 m long; unslotted; according to en 60715	1
210-197	Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; according to en 60715	1
210-198	Copper carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to en 60715	1
210-504	Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; galvanized; according to EN 60715	1
210-505	Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; galvanized; according to EN 60715	1
210-506	Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; galvanized; ähnlich EN 60715	1
210-508	Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; galvanized; ähnlich EN 60715	1

Accessories

Marking accessories

Item no.	Description	Pack. unit (Sub Pack)
209-501	WSB quick marking system; plain; for terminal block width 5 - 17.5 mm; 10 strips with 10 markers per card	5
209-501/000-002	WSB quick marking system; plain; for terminal block width 5 - 17.5 mm; 10 strips with 10 markers per card	5
209-501/000-005	WSB quick marking system; plain; for terminal block width 5 - 17.5 mm; 10 strips with 10 markers per card	5
209-501/000-006	WSB quick marking system; plain; for terminal block width 5 - 17.5 mm; 10 strips with 10 markers per card	5
209-501/000-007	WSB quick marking system; plain; for terminal block width 5 - 17.5 mm; 10 strips with 10 markers per card	5
209-501/000-012	WSB quick marking system; plain; for terminal block width 5 - 17.5 mm; 10 strips with 10 markers per card	5
209-501/000-017	WSB quick marking system; plain; for terminal block width 5 - 17.5 mm; 10 strips with 10 markers per card	5
209-501/000-023	WSB quick marking system; plain; for terminal block width 5 - 17.5 mm; 10 strips with 10 markers per card	5
209-501/000-024	WSB quick marking system; plain; for terminal block width 5 - 17.5 mm; 10 strips with 10 markers per card	5
210-148	Angled support bracket; without screw	10

General accessory

Item no.	Description	Pack. unit (Sub Pack)
210-149	Screw m 5 x 8; for angled support bracket	20
210-720	Operating tool with partially insulated shaft; Type 2, blade (3.5 x 0.5) mm; suitable for 260, 261, 262, 264, 270, 280, 281, 290, 775, 776, 777, 769, 780, 781, 869, 870, 880, 2002, 2003, 2004, 2005 and 2022 Series	1

Images & drawings



Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.