

Item no.: 260-334  
 Product description: 4-CONDUCTOR TERMINAL BLOCK WITH FIXING FLANGE  
 MOUNTING ADAPTER AVAILABLE FOR TS 35 (2012) FOR  
 SCREW OR SIMILAR MOUNTING TYPES 3.2 MM Ø



Packing unit 300 6\*50 pieces

Product group	9 (Std Chassis Mt Blocks)
Cross section [mm <sup>2</sup> ]	0.08- 1.5 mm <sup>2</sup>
Cross section [AWG]	28 - 16 AWG
Connection method	CAGE CLAMP® CONNECTION
Number of strands	2
Measured voltage EN	400 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	18 A
Weight	2.51 g
Color	blue
Wiring type	Sideentry
No. of connection Points	4
No. of potentials	1
Height	17 mm
Height	0.669 in
Width	8 mm
Width	0.315 in
Depth	25 mm
Depth	0.985 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in