

Item no.: 280-619
 Product description: TERMINAL BLOCK FOR PLUGGABLE MODULES 2
 CONDUCTOR TERMINAL BLOCKS 17 MM / 0.663 IN WIDE
 ORANGE SEPARATOR



Packing unit 1 piece

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.08- 2.5 mm ²
Cross section [AWG]	28 - 14 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	400 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	10 A
Weight	16.178 g
Color	gray
Wiring type	Frontentry
No. of connection Points	2
No. of potentials	2
Height	28 mm
Height	1.1 in
Width	17 mm
Width	0.669 in
Depth	50 mm
Depth	1.97 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35