

Item no.: 280-684  
 Product description: 3-CONDUCTOR THROUGH TERMINAL BLOCK SUITABLE FOR EX I APPLICATIONS



Packing unit 100 pieces

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm <sup>2</sup> ]	0.08- 2.5 mm <sup>2</sup>
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	24 A
Weight	7.66 g
Color	blue
Wiring type	Frontentry
No. of connection Points	3
No. of potentials	1
Height	28 mm
Height	1.1 in
Width	5 mm
Width	0.197 in
Depth	64 mm
Depth	2.52 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35