

**Connecting elements**  
**H16,0/15**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



For conductors from 10.0 to 185.0 mm<sup>2</sup> (AWG 7 - 350 MCM)  
tin-plated copper  
dimensional tolerances to DIN 46228 part 1  
• supplied loose in poly-bag

**General ordering data**

Type	H16,0/15
Order No.	<a href="#">0124300000</a>
Version	Wire-end ferrule, uninsulated, 15 mm
GTIN (EAN)	4008190162993
Qty.	500 pc(s).
Packaging	loose

**Data sheet**

**Connecting elements  
H16,0/15**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	15 mm	Width (inches)	0.591 inch
Net weight	0.502 g		

**Technical data**

Version	uninsulated
---------	-------------

**Wire-end ferrules**

Collar diameter (D2)	7.5 mm	Conductor cross-section	16 mm <sup>2</sup>
Contact surface diameter (D1)	5.8 mm	L1 in mm	15 mm
Stripping length	15 mm	Wire connection cross section AWG, max.	AWG 6

**Classifications**

ETIM 6.0	EC000005	ETIM 7.0	EC000005
eClass 9.0	27-40-02-01	eClass 9.1	27-40-02-01
eClass 10.0	27-40-02-01	UNSPSC	31-16-31-02

**Approvals**

Approvals	
ROHS	Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**Connecting elements  
H16,0/15**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings**

