

**SAK Series  
QL 4 SAK6N**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image****Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	QL 4 SAK6N
Order No.	<a href="#">0194500000</a>
Version	SAK Series, Cross-connector, for cross-connection link, Number of poles: 4
GTIN (EAN)	4008 190025601
Qty.	50 pc(s).

## Data sheet

### SAK Series QL 4 SAK6N

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	29.7 mm	Width (inches)	1.169 inch
Height	6 mm	Height (inches)	0.236 inch
Depth	1 mm	Depth (inches)	0.039 inch
Net weight	1.16 g		

### Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

### Material data

Material	Copper	Colour	grey
----------	--------	--------	------

### System specifications

Version	for cross-connection link
---------	---------------------------

### Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

### Dimensions

Pitch in mm (P)	7.9 mm
-----------------	--------

### Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
eClass 9.0	27-14-11-40	eClass 9.1	27-14-11-40
eClass 10.0	27-14-11-40	UNSPSC	30-21-18-01

### Approvals

Approvals



ROHS	Conform
------	---------

### Downloads

Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>