

**SAK Series
HP 2 ADP2**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Building installation wiring

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

General ordering data

Type	HP 2 ADP2
Order No.	0485660000
Version	SAK Series, Fixing plate, beige, 3 mm
GTIN (EAN)	4008190181697
Qty.	20 pc(s).

**SAK Series
HP 2 ADP2**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	3 mm	Width (inches)	0.118 inch
Height	59.5 mm	Height (inches)	2.343 inch
Depth	70.2 mm	Depth (inches)	2.764 inch
Net weight	4.65 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Material data

Material	PA 66	Colour	beige
UL 94 flammability rating	V-2		

System specifications

Version	End and intermediate plate
---------	----------------------------

Additional technical data

Installation advice	Direct mounting	Snap-on	Yes
---------------------	-----------------	---------	-----

Dimensions

Mounting offset	12.5 mm
-----------------	---------

Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
eClass 9.0	27-14-11-33	eClass 9.1	27-14-11-33
eClass 10.0	27-14-11-33	UNSPSC	30-21-18-27

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
User Documentation	StorageConditionsTerminalBlocks