

**W-Series
WQV 10/10**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	WQV 10/10
Order No.	1052460000
Version	W-Series, Cross-connector, For the terminals, Number of poles: 10
GTIN (EAN)	4008 190152 130
Qty.	20 pc(s).

Data sheet

**W-Series
WQV 10/10**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	7.55 mm	Width (inches)	0.297 inch
Height	96.1 mm	Height (inches)	3.783 inch
Depth	18 mm	Depth (inches)	0.709 inch
Net weight	18.85 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

Material data

Material	PA 66	Colour	yellow
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Installation advice	Direct mounting	Type of fixing	when screwed in
---------------------	-----------------	----------------	-----------------

Cross-connector

Number of cross-connected terminals	10	Rated current, 2-pole	57 A
Rated current, multi-pole	57 A	Tightening torque range for fixing screw	0.5...1.0 Nm
Type	Cross-connector		

Dimensions

Pitch in mm (P)	9.9 mm
-----------------	--------

Rating data

Rated current	63 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
eClass 9.0	27-14-11-40	eClass 9.1	27-14-11-40
eClass 10.0	27-14-11-40	UNSPSC	30-21-18-01

Approvals

Approvals	
ROHS	Conform

Data sheet**W-Series
WQV 10/10**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Downloads**

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	35819_WQV_10-10_DXF.dxf STEP
User Documentation	Beipackzettel_WQV.pdf StorageConditionsTerminalBlocks
