

W-Series, Accessories
WAP WDU2.5N/4N**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.
Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

Type	WAP WDU2.5N/4N
Order No.	1060000000
Version	W-Series, Accessories, End plate
GTIN (EAN)	4008190149154
Qty.	50 pc(s).

Data sheet

W-Series, Accessories WAP WDU2.5N/4N

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	1.5 mm	Height	44 mm
Depth	29.7 mm	Net weight	1.781 g

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C
----------------------------------	--------	----------------------------------	--------

Additional technical data

Installation advice	Feed-through (bushing), Direct mounting	Version	End plate
---------------------	--	---------	-----------

Material data

Material	Wemid	Colour	Dark Beige
UL 94 flammability rating	V-0		

System specifications

Product family	W-Series, Accessories	Mounting rail	none
----------------	-----------------------	---------------	------

Classifications

ETIM 3.0	EC000886	UNSPSC	30-21-18-27
eClass 5.1	27-14-11-33	eClass 6.2	27-14-11-33
eClass 7.1	27-14-11-33		

Approvals

ROHS	Conform
------	---------