

VSSC AP VSSC6

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



End plates (AP) for the VSSC product series in light blue and black

General ordering data

Type	AP VSSC6
Order No.	1063110000
Version	VSSC, End plate
GTIN (EAN)	4032248947553
Qty.	50 pc(s).

Creation date May 11, 2020 2:48:41 PM CEST

Catalogue status 01.05.2020 / We reserve the right to make technical changes.

Data sheet

VSSC AP VSSC6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	1.6 mm	Width (inches)	0.063 inch
Height	88.5 mm	Height (inches)	3.484 inch
Depth	81 mm	Depth (inches)	3.189 inch
Net weight	5.8 g		

Temperatures

Humidity	5...96 %	Operating temperature, max.	70 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	80 °C
Storage temperature, min.	-40 °C	Operating temperature	-40 °C...70 °C
Storage temperature	-40 °C...80 °C		

General data

Colour	black	Design	miscellaneous
Protection degree	IP20	UL 94 flammability rating	V-0
Version	End plate		

Classifications

ETIM 6.0	EC000490	ETIM 7.0	EC000490
eClass 9.1	27-13-92-90	UNSPSC	30-21-18-11

Approvals

Approvals

GOSTEX

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP