

**VSSC
AP VSSC4**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



End plates (AP) for the VSSC product series in light blue and black

General ordering data

Type	AP VSSC4
Order No.	1063 120000
Version	VSSC, End plate
GTIN (EAN)	4032248947560
Qty.	50 pc(s).

Creation date April 23, 2020 6:41:12 AM CEST

Catalogue status 17.04.2020 / We reserve the right to make technical changes.

Data sheet

VSSC AP VSSC4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	1.5 mm	Width (inches)	0.059 inch
Height	76 mm	Height (inches)	2.992 inch
Depth	58.5 mm	Depth (inches)	2.303 inch
Net weight	0.9 g		

Temperatures

Humidity	5...96 %	Operating temperature, max.	70 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	80 °C
Storage temperature, min.	-40 °C	Operating temperature	-40 °C...70 °C
Storage temperature	-40 °C...80 °C		

General data

Colour	black	Design	miscellaneous
UL 94 flammability rating	V-0	Version	End plate

Connection data

Type of connection	Screw connection
--------------------	------------------

Classifications

ETIM 6.0	EC000490	ETIM 7.0	EC000490
eClass 9.1	27-13-92-90	UNSPSC	30-21-18-11

Approvals

Approvals

GOSTEX

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP