

**Screwdriver
SDIS SL 0.6X3.5X100**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Type	SDIS SL 0.6X3.5X100
Order No.	1274660000
Version	Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade thickness (A): 0.6 mm
GTIN (EAN)	4050118072631
Qty.	1 pc(s).

Data sheet

**Screwdriver
SDIS SL 0.6X3.5X100**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	204 mm	Width (inches)	8.031 inch
Net weight	34 g	Diameter	23 mm

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Screwing tools

Blade length	100 mm	Blade thickness (A)	0.6 mm
Blade width (B)	3.5 mm	Form	Slotted

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
eClass 9.0	21-04-04-07	eClass 9.1	21-04-04-07
eClass 10.0	21-04-04-07		

Approvals

Approvals



Downloads

Approval/Certificate/Document of Conformity	Manufacturer's Declaration - Screwdrivers
Brochure/Catalogue	CAT 6 TOOLS 15/16 EN CAT 5 ENCL 17/18 EN CAT 1 TERM 16/17 EN
Engineering Data	STEP

Data sheet

**Screwdriver
SDIS SL 0.6X3.5X100**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Example of use

