

**Screwdriver
SD TO 0,6X3,0**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Slotted screwdriver with rounded blade SD DIN 5265,
ISO 2380/2, output to DIN 5264, ISO 2380/1.
ChromTop tip, SoftFinish grip

General ordering data

Type	SD TO 0,6X3,0
Order No.	1323880000
Version	Screwdriver, Blade width (B): 3 mm, Blade length: 70 mm, Blade thickness (A): 0.6 mm
GTIN (EAN)	4050118127133
Qty.	1 pc(s).

Creation date August 17, 2020 4:41:06 PM CEST

Catalogue status 14.08.2020 / We reserve the right to make technical changes.

Data sheet

**Screwdriver
SD TO 0,6X3,0**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight 34 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Screwing tools

Blade length	70 mm	Blade thickness (A)	0.6 mm
Blade type	A	Blade width (B)	3 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
eClass 9.0	21-04-04-07	eClass 9.1	21-04-04-07
eClass 10.0	21-04-04-07		

Approvals

Approvals



Downloads

Brochure/Catalogue [CAT 4.2 ELECTR 18/19 EN](#)
[CAT 6 TOOLS 15/16 EN](#)
[CAT 5 ENCL 17/18 EN](#)