

**Z-series  
ZBW 1**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image****Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

**General ordering data**

Type	ZBW 1
Order No.	<a href="#">1669620000</a>
Version	Z-series, Operating tool
GTIN (EAN)	4008190429126
Qty.	1 pc(s).

**Z-series  
ZBW 1**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	27.76 mm	Width (inches)	1.093 inch
Height	147 mm	Height (inches)	5.787 inch
Depth	23.75 mm	Depth (inches)	0.935 inch
Net weight	17 g		

**Temperatures**

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-40 °C
Continuous operating temp., max.	100 °C		

**Material data**

Material	POM	Colour	orange
UL 94 flammability rating	HB		

**System specifications**

Version	Operating tool
---------	----------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
--------------------------	----	---------------------	-----------------

**Classifications**

ETIM 6.0	EC000149	ETIM 7.0	EC000149
eClass 9.0	21-04-50-03	eClass 9.1	21-01-90-90
eClass 10.0	21-04-50-03	UNSPSC	30-21-18-11

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
--------------------	---