

**Z-series
ZBWW**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

General ordering data

Type	ZBWW
Order No.	1669630000
Version	Z-series, Operating tool
GTIN (EAN)	4008 190429 119
Qty.	1 pc(s).

Creation date April 26, 2020 6:24:11 PM CEST

Catalogue status 17.04.2020 / We reserve the right to make technical changes.

**Z-series
ZBWW**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	27.76 mm	Width (inches)	1.093 inch
Height	140.18 mm	Height (inches)	5.519 inch
Depth	23.75 mm	Depth (inches)	0.935 inch
Net weight	17.439 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-40 °C
Continuous operating temp., max.	100 °C		

Material data

Material	POM	Colour	orange
UL 94 flammability rating	HB		

System specifications

Version	Operating tool
---------	----------------

Additional technical data

Explosion-tested version	No
--------------------------	----

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
eClass 9.0	21-04-50-03	eClass 9.1	21-01-90-90
eClass 10.0	21-04-50-03	UNSPSC	30-21-18-11

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	STEP
User Documentation	StorageConditionsTerminalBlocks