

ESG ESG 8/17 SYS PRO M WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Similar to illustration



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from the following manufacturers:

- Siemens
- Télémecanique
- ABB
- Beckhoff
- Lumberg
- Tags for all-purpose usage; self-adhesive or clip-on tags, depending on the type

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

Please note that these markers are not intended for printing with the SpeedMarking laser.

General ordering data

| | |
|--------------------|--|
| Type | ESG 8/17 SYS PRO M WS |
| Order No. | 1755340000 |
| Version | ESG, Device markers x 17 mm, PA 66, Colour: white, pluggable |
| GTIN (EAN) | 4032248017577 |
| Qty. | 200 pc(s). |
| compatible printer | 1324380000 2438520000 2438510000 |

ESG
ESG 8/17 SYS PRO M WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Width | 17 mm | Width (inches) | 0.669 inch |
| Height | 8 mm | Height (inches) | 0.315 inch |
| Depth | 0.8 mm | Depth (inches) | 0.031 inch |
| Net weight | 0.515 g | | |

General data

| | | | |
|--|----------------|-----------------------------|--------------|
| Application/manufacturer | AEG, ABB-Stotz | Colour | white |
| Halogen | No | Material | PA 66 |
| Material colour according to resistance code | 9 | Operating temperature range | -40...100 °C |
| UL 94 flammability rating | V-2 | Version | pluggable |
| Width | 17 mm | | |

Classifications

| | | | |
|-------------|-------------|------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| eClass 9.0 | 27-40-06-29 | eClass 9.1 | 27-40-06-29 |
| eClass 10.0 | 27-40-06-29 | UNSPSC | 30-21-18-01 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | EPLAN, WSCAD |
| Engineering Data | STEP |
| Software | M-Print PRO configuration file |

Data sheet

ESG
ESG 8/17 SYS PRO M WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

