

**Bolt-type screw terminals
ADP WF10/WF12**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Klippon® Connect with stud Technology

Our stud terminals are an established, robust connection alternative for particularly harsh environments. The extensive accessories and quality workmanship ensure high productivity in planning and installation – and sustainable safety in operation..

General ordering data

Type	ADP WF10/WF12
Order No.	1780940000
Version	Bolt-type screw terminals, Cover profile, Transparent, 1000 mm
GTIN (EAN)	4032248241255
Qty.	1 m

Creation date August 8, 2020 8:50:20 AM CEST

Catalogue status 24.07.2020 / We reserve the right to make technical changes.

Bolt-type screw terminals ADP WF10/WF12

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	1,000 mm	Width (inches)	39.37 inch
Height	51.4 mm	Height (inches)	2.024 inch
Depth	6.05 mm	Depth (inches)	0.238 inch
Net weight	80 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

Material data

Material	Polycarbonate	Colour	Transparent
UL 94 flammability rating	V-2		

Additional technical data

Snap-on	Yes
---------	-----

Dimensions

Fixing dimension	7 mm
------------------	------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
eClass 9.0	27-14-11-92	eClass 9.1	27-14-11-92
eClass 10.0	27-14-11-92	UNSPSC	30-21-18-27

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
User Documentation	StorageConditionsTerminalBlocks