

**RIDERSERIES RCM
SCM-I CLIP N**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Plastic retaining clip for RIDERSERIES RCM relays

General ordering data

Type	SCM-I CLIP N
Order No.	8875620000
Version	RIDERSERIES RCM, Retaining clip
GTIN (EAN)	4032248608577
Qty.	10 pc(s).

Creation date April 22, 2020 8:13:38 AM CEST

Catalogue status 17.04.2020 / We reserve the right to make technical changes.

Data sheet

**RIDERSERIES RCM
SCM-I CLIP N**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	27 mm	Width (inches)	1.063 inch
Height	24 mm	Height (inches)	0.945 inch
Depth	55.5 mm	Depth (inches)	2.185 inch
Net weight	3.74 g		

Temperatures

Humidity	40 °C / 93 % rel. humidity, no condensation	Operating temperature, max.	70 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C	Operating temperature	-40 °C...70 °C
Storage temperature	-40 °C...85 °C		

General data

Version	for low screw connection base	Material	Plastic
Colour	orange		

Classifications

ETIM 6.0	EC002586	ETIM 7.0	EC002586
eClass 9.1	27-37-16-92	eClass 10.0	27-37-16-92
UNSPSC	30-21-19-17		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 4.2 ELECTR 18/19 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

Data sheet

**RIDERSERIES RCM
SCM-I CLIP N**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Dimensional drawing

