

**Tools**  
**M-D-STRIPAX +6 MEHA**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

**General ordering data**

Type	M-D-STRIPAX +6 MEHA
Order No.	<a href="#">9003500000</a>
Version	Tools, Stripping and cutting tool, Conductor with custom insulation, 7mm
GTIN (EAN)	4008190107109
Qty.	1 pc(s).

Creation date August 7, 2020 10:29:53 PM CEST

Catalogue status 24.07.2020 / We reserve the right to make technical changes.

## Tools M-D-STRIPAX +6 MEHA

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	82 mm	Width (inches)	3.228 inch
Height	135 mm	Height (inches)	5.315 inch
Depth	16 mm	Depth (inches)	0.63 inch
Weight	110 g	Net weight	106.38 g

### Environmental Product Compliance

REACH SVHC Lead 7439-92-1

### Stripping tools

Cable type	Conductor with custom insulation	Max. conductor diameter	1.3 mm
Min. conductor diameter	0.2 mm	Stripping length, max.	7 mm
Stripping range AWG, max.	18 AWG	Stripping range AWG, min.	32 AWG

### Classifications

ETIM 6.0	EC002109	ETIM 7.0	EC002109
eClass 9.0	21-04-37-06	eClass 9.1	21-04-37-06
eClass 10.0	21-04-37-06	UNSPSC	23-17-16-04

### Downloads

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)

**Data sheet**

**Tools**  
**M-D-STRIPAX +6 MEHA**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Example of use**

