

**Connecting elements**  
**H2,5/10**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



For conductors from 0.25 to 6,0 mm<sup>2</sup> (AWG 24 - 10)  
tin-plated copper  
dimensional tolerances to DIN 46228 part 1  
• supplied loose in polybag

**General ordering data**

Type	H2,5/10
Order No.	<a href="#">9004080000</a>
Version	Wire-end ferrule, uninsulated, 10 mm
GTIN (EAN)	4008 190 145446
Qty.	1,000 pc(s).
Packaging	loose

Creation date August 7, 2020 10:47:46 PM CEST

Catalogue status 24.07.2020 / We reserve the right to make technical changes.

## Data sheet

### Connecting elements H2,5/10

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Net weight 0.098 g

### Technical data

Version uninsulated

### Wire-end ferrules

Collar diameter (D2)	3.4 mm	Conductor cross-section	2.5 mm <sup>2</sup>
Contact surface diameter (D1)	2.2 mm	L1 in mm	10 mm
Stripping length	10 mm	Wire connection cross section AWG, max.	AWG 14

### Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
eClass 9.0	27-40-02-01	eClass 9.1	27-40-02-01
eClass 10.0	27-40-02-01	UNSPSC	31-16-31-02

### Approvals

Approvals



ROHS Conform

### Downloads

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**Connecting elements**  
**H2,5/10**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings**

