

**Connecting elements
H4,0/22D ZH GR SV**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- in multi-pack bag (5 x 100 pcs.)
- DIN colour code
- other colour code

General ordering data

Type	H4,0/22D ZH GR SV
Order No.	9004730000
Version	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, grey
GTIN (EAN)	4008 19016 1811
Qty.	100 pc(s).
Packaging	Multipack bag

Creation date September 28, 2020 3:11:01 PM CEST

Catalogue status 11.09.2020 / We reserve the right to make technical changes.

Connecting elements H4,0/22D ZH GR SV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight 0.54 g

Technical data

Version Twin wire-end ferrule

Wire-end ferrules

Collar height (A)	9 mm	Collar width (B)	5.2 mm
Colour code	DIN	Conductor cross-section	4 mm ²
Contact surface diameter (D1)	3.5 mm	Contact surface length (L2)	12 mm
L1 in mm	22 mm	Metal sleeve thickness (S1)	0.2 mm
Plastic collar thickness (S2)	0.5 mm	Stripping length	15 mm
Wire connection cross section AWG, max.	AWG 12		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
eClass 9.0	27-40-02-01	eClass 9.1	27-40-02-01
eClass 10.0	27-40-02-01	UNSPSC	31-16-31-02

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
User Documentation	Technical information - EN Technical information - DE

Data sheet

**Connecting elements
H4,0/22D ZH GR SV**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Drawing

