

## Connecting elements H0,14/10 GR SV

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



- Weidmüller colour code
- in multipack bag ( 5 x 100 pcs.)

### General ordering data

Type	H0,14/10 GR SV
Order No.	<a href="#">9005180000</a>
Version	Wire-end ferrule, insulated, 8 mm, 6 mm, grey
GTIN (EAN)	4008190859909
Qty.	500 pc(s).
Packaging	Multipack bag

**Data sheet**

**Connecting elements  
H0,14/10 GR SV**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	10 mm	Width (inches)	0.394 inch
Net weight	0.048 g		

**Technical data**

Version	insulated
---------	-----------

**Wire-end ferrules**

Collar diameter (D2)	1.5 mm	Colour code	Weidmüller
Conductor cross-section	0.14 mm <sup>2</sup>	Contact surface diameter (D1)	0.6 mm
Contact surface length (L2)	6 mm	L1 in mm	10 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	8 mm	Wire connection cross section AWG, max.	AWG 26

**Classifications**

ETIM 6.0	EC000005	ETIM 7.0	EC000005
eClass 9.0	27-40-02-01	eClass 9.1	27-40-02-01
eClass 10.0	27-40-02-01	UNSPSC	31-16-31-02

**Approvals**

Approvals	
ROHS	Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**Connecting elements**  
**H0,14/10 GR SV**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings**

**Drawing**

