

**Screwdriver
SDIS 0.4X2.5X75**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Type	SDIS 0.4X2.5X75
Order No.	9008370000
Version	Screwdriver, Blade width (B): 2.5 mm, Blade length: 75 mm, Blade thickness (A): 0.4 mm
GTIN (EAN)	4032248056330
Qty.	1 pc(s).

Data sheet

**Screwdriver
SDIS 0.4X2.5X75**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	179 mm	Width (inches)	7.047 inch
Weight	33 g	Net weight	28.5 g
Diameter	23 mm		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Screwing tools

Blade length	75 mm	Blade thickness (A)	0.4 mm
Blade type	A	Blade width (B)	2.5 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
eClass 9.0	21-04-04-07	eClass 9.1	21-04-04-07
eClass 10.0	21-04-04-07	UNSPSC	27-11-17-01

Approvals

Approvals



Downloads

Approval/Certificate/Document of Conformity	Manufacturer's Declaration - Screwdrivers Declaration of the Manufacturer
Brochure/Catalogue	CAT 6 TOOLS 15/16 EN CAT 5 ENCL 17/18 EN CAT 1 TERM 16/17 EN CAT 2 PORTFOLIOGUIDE EN