

**Screwdriver  
SDIS 0.6X3.5X100**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

**General ordering data**

Type	SDIS 0.6X3.5X100
Order No.	<a href="#">9008390000</a>
Version	Screwdriver, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade thickness (A): 0.6 mm
GTIN (EAN)	4032248056354
Qty.	1 pc(s).

**Data sheet**

**Screwdriver  
SDIS 0.6X3.5X100**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	205 mm	Width (inches)	8.071 inch
Weight	41 g	Net weight	35 g
Diameter	23 mm		

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Screwing tools**

Blade length	100 mm	Blade thickness (A)	0.6 mm
Blade type	B	Blade width (B)	3.5 mm
Form	Slotted		

**Classifications**

ETIM 6.0	EC000158	ETIM 7.0	EC000158
eClass 9.0	21-04-04-07	eClass 9.1	21-04-04-07
eClass 10.0	21-04-04-07	UNSPSC	27-11-17-01

**Approvals**

Approvals



**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">Manufacturer's Declaration - Screwdrivers Declaration of the Manufacturer</a>
Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a> <a href="#">CAT 5 ENCL 17/18 EN</a> <a href="#">CAT 1 TERM 16/17 EN</a> <a href="#">CAT 2 PORTFOLIOGUIDE EN</a>