

**Pressing tool
HTF SUB-D**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Crimping tools for SUB-D contacts**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

General ordering data

Type	HTF SUB-D
Order No.	9013260000
Version	Pressing tool, Crimping tool for contacts, FoderBcrimp
GTIN (EAN)	4008 190056896
Qty.	1 pc(s).

Creation date July 22, 2020 2:20:10 AM CEST

Data sheet

**Pressing tool
HTF SUB-D**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Weight	438 g	Net weight	440.98 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Version	Mechanical, without interchangeable inserts
---------	---

Description of contact

Type of contact	SUB-D	Conductor cross-section, max. AWG	AWG 20
Conductor cross-section, min. AWG	AWG 28		

tool data crimping

Crimping profile 1, min.	28 AWG	Crimping type/profile	FoderBcrimp
Crimping profile 1, max.	24 AWG	Crimping profile 2, min.	22 AWG
Crimping profile 2, max.	20 AWG		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
eClass 9.0	21-04-38-11	eClass 9.1	21-04-38-11
eClass 10.0	21-04-38-11	UNSPSC	23-17-16-04

Approvals

Approvals



Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
--------------------	--------------------------------------

Data sheet

**Pressing tool
HTF SUB-D**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

