

**Connecting elements
H4,0/26D GR**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- supplied loose in polybag
- DIN colour code
- other colour code

General ordering data

Type	H4,0/26D GR
Order No.	9019210000
Version	Wire-end ferrule, insulated, 20 mm, 18 mm, grey
GTIN (EAN)	4008 190002336
Qty.	100 pc(s).
Packaging	loose

Creation date August 8, 2020 1:49:47 AM CEST

Catalogue status 24.07.2020 / We reserve the right to make technical changes.

**Connecting elements
H4,0/26D GR**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Net weight 0.38 g

Technical data

Version insulated

Wire-end ferrules

Collar diameter (D2)	4.8 mm	Colour code	DIN
Conductor cross-section	4 mm ²	Contact surface diameter (D1)	2.8 mm
Contact surface length (L2)	18 mm	L1 in mm	26 mm
Metal sleeve thickness (S1)	0.2 mm	Military designation	T 20A 021 A
Plastic collar thickness (S2)	0.3 mm	Stripping length	20 mm
Wire connection cross section AWG, max.	AWG 12		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
eClass 9.0	27-40-02-01	eClass 9.1	27-40-02-01
eClass 10.0	27-40-02-01	UNSPSC	31-16-31-02

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
User Documentation	Technical information - EN Technical information - DE

Data sheet

**Connecting elements
H4,0/26D GR**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Drawing

