

Accessories
BIT E6,3 0,8X4,0X70**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection
Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126

General ordering data

Type	BIT E6,3 0,8X4,0X70
Order No.	9024030000
Version	Screwdriver insert, Blade width (B): 4 mm, Blade length: 70 mm, Blade thickness (A): 0.8 mm
GTIN (EAN)	4008 190852658
Qty.	5 pc(s).

Creation date August 7, 2020 3:57:48 AM CEST

Catalogue status 24.07.2020 / We reserve the right to make technical changes.

Data sheet

Accessories BIT E6,3 0,8X4,0X70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	70 mm	Width (inches)	2.756 inch
Weight	10.6 g	Net weight	10.3 g

Screwing tools

Blade length	70 mm	Blade thickness (A)	0.8 mm
Blade width (B)	4 mm	Form	E 6.3 DIN 3126, Slotted

Classifications

ETIM 6.0	EC002116	ETIM 7.0	EC002116
eClass 9.1	21-04-04-90	eClass 10.0	21-04-04-90
UNSPSC	27-11-28-14		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
--------------------	--------------------------------------