

Rail Mounted Terminal Blocks

9908500000

When good enough just isn't good enough



KDKS 1 (with BFI/disconnect)

[Email to a Friend](#)


Representative Photo

Technical Information

Clamping Type	Screw Clamp
Series	SAK Series W Series
Rail Type	Combi Foot
Function	Circuit Protection
Configuration	Fuse and Feed Through Single Level
Wire Size	#22...12 AWG
Current	10 A upper level, 20 A lower level
Voltage	300 V
Color/Material	Beige PA
Special Requirements	Blown fuse indication 24 VDC Hinge (-)

Technical Data

	UL	CSA	VDE
Rated Voltage	300 V	300 V	500 V
Rated Current	10 A 20 A	10 A 25 A	
Wire Size	#22...12 AWG	#22...12 AWG	4 mm ²

Additional Data

Width/Length/Height mm (in.)	8/73.5/55.7 (.31"/2.89"/2.19")
Insulation Stripping Length mm (in.)	9 (.35")
Torque Nm (lb. in)	0.6 (5.5)
Clamping Screw	M 3
Flammability Class	UL 94 (V2)

Suggested Accessories

DIN-rail
End bracket
End plate/partition (AP/TW)
Ferrules
Fuses
Marking pens
Marking tags (DEK)

Mounting brackets

Tools

Product Liability The above information describes our products. It does not constitute guaranteed properties and is not intended to affirm the suitability of a product for a particular application. Regrettably, omissions and exceptions cannot be completely ruled out. Technical data are always specified by their average values. Exact data and the tolerances which apply to our processes can be requested from:

Weidmüller - North America
United States 001 (800) 849-9343
Canada 001 (800) 268-4080

or

Weidmüller - Germany
Telephone operator 0049 (-5252) 960-0