

## Installation Products

### ClipCard - Equipment Marker

# NEW



The new generation of Weidmüller ClipCard equipment markers offer an interesting alternative to engravings.

- Professional marking of cards in checker card design
- Advanced printing quality through thermal transfer technology
- Single card modules can be separated by breaking off the checker card and are ready for use immediately
- Complete system of card plus card holder as well as protective strip for use in aggressive environment
- Mounting rail with protective strip for extra-long marking purposes
- High flexibility through "just-in-time" production of the equipment marking
- Standard dimension of the markers of 15 mm, in four different length variants
- Can also be printed with the Weidmüller plotter system

#### United States

Weidmüller Inc.  
821 Southlake Blvd.  
Richmond, Virginia 23236  
Telephone: (800) 849-9343  
Facsimile: (804) 379-2593  
Email: [info@weidmuller.com](mailto:info@weidmuller.com)  
Website: [www.weidmuller.com](http://www.weidmuller.com)

#### Canada

Weidmüller Ltd.  
10 Spy Court  
Markham, Ontario L3R-5H6  
Telephone: (800) 268-4080  
Facsimile: (905) 475-2798  
Email: [info1@weidmuller.ca](mailto:info1@weidmuller.ca)  
Website: [www.weidmuller.ca](http://www.weidmuller.ca)

#### Mexico

Weidmüller, S.A. de C.V.  
5 Sur No. 4311  
Col. Huexotitla  
72534 Puebla, Pue. Mexico  
Telephone: (22) 37 2549  
Facsimile: (22) 43 1981  
Email: [weidmull@acnet.net](mailto:weidmull@acnet.net)

# ClipCard - Equipment Marker



## Technical data

Application	Card and card holder
Material	Protective strip
	Mounting rail
Flammability class	UL94 V2
Color	Silver, white
	Card holder
	Protective strip
Temperature range	- 40°...+ 100 °C
Print	Thermal transfer or plotter
Printing device	ThermoCard printer, plotter plus Inlay
ClipCard dimensions	15 x 17 mm (.59 x .67 in.)
	15 x 25 mm (.59 x .98 in.)
	15 x 49 mm (.59 x 1.93 in.)
	15 x 67 mm (.59 x 2.64 in.)

## Ordering Data

### Type

CC 15/17 blank ws	1789850000
CC 15/17 blank si	1789860000
CC 15/27 blank ws	1789820000
CC 15/27 blank si	1789840000
CC 15/27 blank trans.	1789830000
CC 15/49 blank ws	1789880000
CC 15/49 blank si	1789890000
CC 15/49 blank trans.	1789900000
CC 15/67 blank ws	1789910000
CC 15/67 blank si	1789920000
CC 15/67 blank trans.	1789930000
CC-H 15/17	1790430000
CC-H 15/27	1790410000
CC-H 15/49	1790420000
CC-H 15/67	1790400000
CC-Rail 1000	1790150000
CC-Rail transpar. 1000	1790160000
THC-Sample bag	1790450000
Equipment/Software	
Thermocard Printer	1774070000
M-Label software for Windows	1789550000

## Installation and equipment marking

PA6.6
PC
PVC
UL94 V2
Silver, white
Black
Transparent
- 40°...+ 100 °C
Thermal transfer or plotter
ThermoCard printer, plotter plus Inlay
15 x 17 mm (.59 x .67 in.)
15 x 25 mm (.59 x .98 in.)
15 x 49 mm (.59 x 1.93 in.)
15 x 67 mm (.59 x 2.64 in.)

### Part No.

1789850000
1789860000
1789820000
1789840000
1789830000
1789880000
1789890000
1789900000
1789910000
1789920000
1789930000
1790430000
1790410000
1790420000
1790400000
1790150000
1790160000
1790450000
1774070000
1789550000