

Data sheet

Tools

Cutter-Stripper

NEW



Cutter-Stripper AWG 22...10

Cutter-Stripper AWG 30...20

- 1 Stripping holes:** Precision ground stripping holes and easy-to-read markings.
- 2 Wire Cutter:** Smooth cutting of wires.
- 3 Strong gripping nose:** Easy bending and pulling of wires.
- 4 Optimum ergonomics:** Head of tool and handles designed at optimum 22 degree angle to prevent awkward wrist bends.
- 5 Spring-loaded closure:** Coil spring provides fast self-opening action.

Great Britain

Weidmüller Ltd
Klippon House
Centurion Court Office
Meridian East,
Meridian Business Park
Leicester, LE19 1TP
Phone +44 1162 823470
Fax +44 1162 893582
marketing@weidmuller.co.uk

United States

W-Interconnections Inc.
821 Southlake Boulevard,
Virginia - Richmond 23236
Phone +1 804 7942877
Fax +1 804 3792593
info@weidmuller.com
www.weidmuller.com

Canada

W Interconnections Canada Ltd.
10 Spy Court, Markham,
Ontario L3 R5 H6
Phone +1 905 475-1507
Fax +1 905 475-2798
info1@weidmuller.ca
www.weidmuller.ca

Other countries

Weidmüller Interface GmbH & Co. KG
Postfach 3030
32720 Detmold
Klingenbergstraße 16
32758 Detmold
Phone +49 5231 14-0
Fax +49 5231 14-292083
info@weidmueller.de
www.weidmueller.com

Stripping Tools

- Precision ground stripping holes
- Self-opening
- Wire cutter

Cutter-Stripper AWG 22...10



Stripping of THHN, MTW, PVC and other wire insulations

AWG 22...10

- Precision ground stripping holes
- Smooth cutting of wires
- Strong gripping nose
- Easy-to-read markings
- 22 degree angle for optimum ergonomics
- Self-opening



Technical data

Max. stripping capacity	
Conductor cross-section	AWG
Tool data	
Length	mm
Weight	mm
Note	

Ordering data

Version
Note

Cutter-Stripper AWG 30...20



Stripping of THHN, MTW, PVC and other wire insulations

AWG 30...20

- Precision ground stripping holes
- Smooth cutting of wires
- Strong gripping nose
- Easy-to-read markings
- 22 degree angle for optimum ergonomics
- Self-opening



CS 22-10		
22...10		
180		
150		

Type	Qty.	Order No.
CS 22-10	1	1338810000

CS 30-20		
30...20		
180		
150		

Type	Qty.	Order No.
CS 30-20	1	1338800000