

RTM 030 K MS

Product no.: T0054462199N



Benefits

- › Widest range of geometrics and sizes
Covers all standard applications. One tool meets all operational needs.
- › MIL-SPC / IPC standard (potential free)
Reduces risk of damage to sensitive micro components and workpieces. No rework, lower total cost of ownership
- › Active tip technology Fastest heat-up and recovery time, sensor close to the solder tip, excellent heat transfer. No downtime, continuing workflow, excellent results
- › Digital tool for data storage Motion activated usage sensor for energy control and data storage
- › Patented tip & grip design Only soldering tip on the market which can be changed without a tool. 20% faster change than leading competitors.

**Technical Data**

Tip shape	Knife
Tip type	MS
Width in mm	0.9
Width in inches	0.035
Thickness in mm	2.2
Thickness in inches	55.88
Length mm	20
Length inches	0.787
Power	40 W
Packaging unit	1