

# WR3000M

3-Channel Power Unit, 360 W (400 W)  
Product no.: WR3000MN



## Benefits

- WR3M multi-channel, hot air, desoldering, soldering rework system
- 400 watts of power over 3 independently-controlled channels
- Application flexibility with up to 21 tool options
- PC Connectivity and data logging software included





### Technical Data

Dimensions L x W x H (mm)	280 x 240 x 103
Dimensions L x W x H (inches)	11,02 x 9,45 x 4,06
Weight (approx.) in kg	7.3
Voltage	120 V
Power	400 W
Channels	3
Temperature range (depends on tool) °C	93 - 454
Temperature range (depends on tool) °F	200 - 850
Temperature accuracy °C	±9°C
Temperature accuracy °F	±17°F
Temperature stability °C	±2°C
Temperature stability °F	±4°F
Equipotential bonding socket	Via 3.5 mm pawl socket on back of device (Hard grounded)
Display	---
Air consumption l/min	---
Operating pressure in bar/psi	---
Capacity l/min	18
Vacuum	0,7 bar, max