

COOPER LIGHTING - METALUX®

DIMENSIONS (2)

Wall Bracket Series



Wall Cloud Series



DESCRIPTION

The Metalux Residential Wall Bracket Series is an energy efficient luminaire designed for versatility in application and performance. The series feature an opal white acrylic refractor that produces a 180° uniform light distribution pattern. The versatile Wall Bracket Series combines quality and economy in a multi-purpose wall bracket. The luminaire is perfect for illuminating corridors, stairwells, lavatories, dressing rooms, basements, utility/task and area lighting.

The Wall Cloud Series incorporates a vacuum formed soft white acrylic lens for more residential appeal.





WALL BRACKET WALL CLOUD SERIES

2', 3' or 4' 1 or 2 Lamps

RESIDENTIAL ALL PURPOSE WALL BRACKETS

- Uses one or two fluorescent lamps (not included)
- Contemporary styling
- · Die formed steel housing
- · Baked white enamel finish
- Extruded smooth opal white acrylic refractor
- 180° uniform light distribution
- Decorative opaque injection molded white end plates
- · Easy wiring access
- Vertical wall or horizontal ceiling mounting application
- Suitable for damp locations
- UL/CUL Listed

ORDERING INFORMATION (4)

Catalog Number (1, 3, 5)	Description	Shipping Wt.
(WITH WHITE ENDS / 1 LIGHT)		
6212	1 lamp 24", 20W T12	7 lbs. (3.2kg)
6313	1 lamp 36", 30W T12	9 lbs. (4.1kg)
6414	1 lamp 48", 40W T12	12 lbs. (5.4kg)
(WITH WHITE ENDS / 2 LIGHT)		
6222	2 lamp 24", 20W T12	7 lbs. (3.2kg)
6424	2 lamp 48", 40W T12	12 lbs. (5.4kg)
(WALL CLOUD)		
6232	2 lamp 24", 20W T12	8 lbs. (3.6kg)
6434	2 lamp 48", 40W T12	13 lbs. (5.9kg)
6434E ⁽³⁾	2 lamp 48" with LE3, 40W T12	13 lbs. (5.9kg)
6434-REB1	2 lamp 48" with LE3, 32W T8	13 lbs. (5.9kg)