

Weller®

HIGH-PERFORMANCE LED SOLDERING IRONS

LIGHT DUTY



**Test Equipment
Depot**
1-800-517-8431

99 Washington Street
Melrose, MA 02176
Phone 781-665-1400
Toll Free 1-800-517-8431

Visit us at www.TestEquipmentDepot.com

15-WATT LED SOLDERING IRON



Three 5mm high-temperature, long-life LEDs at 25 lumens/ft² for superior soldering accuracy and application illumination



Co-molded, soft-grip ribbed handle design for maximum comfort and reduced slippage



Triangular area for maximum of tip control and round handle for ease of tip rotation



High-performance, stainless-steel heater technology with heat up to 750°F



A 7-year warranty, longest in the industry



Cord strain relief for extended life



Possible applications: micro-components, electronic kits, low-voltage wiring, wire connection <18 AWG (0.04" diameter)



UL Listed – cUL available

IMPORTANT: use only Weller® tips



PRODUCT DETAILS

Catalog number:	SP15NUS
UPC number:	03703266842
Type:	Non-temperature controlled
Wattage:	15W
Temperature:	750° F / 400° C
Cord length:	5 feet
Iron tip:	S5, screwdriver, 0.078"
Package includes:	Peg hook, retail packaging, iron stand, user manual
Compatible tips:	S3, screwdriver, 0.138" S31*, conical, 0.015" S32*, screwdriver, 0.078" *Long-life tips
Stock item:	Normal stock item
Packaging (LxWxH):	11" x 4.25" x 1.89"
Gross weight:	0.317 lbs.

A family of wattages: **15** **25** **40** **80** Find your favorite.

