

Home → Tool Types → Screwdrivers → Precision Slotted Screwdrivers

Precision Slotted Screwdrivers



Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Be the first to review this product

Filter:

| SKU | Product | Size Slotted | OAL MM | Blade Length Inch | Price | Qty |
|-------|---------------------------------------|--------------|--------|-------------------|-------|-----|
| 26008 | Precision Slotted .80 (1/32") x 40mm | 0.8mm | 120 | 1.6 | | 0 |
| 26010 | Precision Slotted 1.0 (.039") x 40mm | 1.0mm | 120 | 1.6 | | 0 |
| 26012 | Precision Slotted 1.2 (3/64") x 40mm | 1.2mm | 120 | 1.6 | | 0 |
| 26015 | Precision Slotted 1.5 (1/16") x 40mm | 1.5mm | 120 | 1.6 | | 0 |
| 26018 | Precision Slotted 1.8 (.070") x 40mm | 1.8mm | 120 | 1.6 | | 0 |
| 26020 | Precision Slotted 2.0 (5/64") x 40mm | 2.0mm | 120 | 1.6 | | 0 |
| 26022 | Precision Slotted 2.0 (5/64") x 50mm | 2.0mm | 145 | 2 | | 0 |
| 26023 | Precision Slotted 2.0 (5/64") x 100mm | 2.0mm | 180 | 3.9 | | 0 |
| 26025 | Precision Slotted 2.5 (3/32") x 50mm | 2.5mm | 145 | 2 | | 0 |
| 26027 | Precision Slotted 2.5 (3/32") x 100mm | 2.5mm | 195 | 3.9 | | 0 |

| SKU | Product | Size Slotted | OAL MM | Blade Length Inch | Price | Qty |
|-------|---------------------------------------|--------------|--------|-------------------|-------|---|
| 26028 | Precision Slotted 2.5 (3/32") x 150mm | 2.5mm | 245 | 6 | | 0  |
| 26030 | Precision Slotted 3.0 (1/8") x 50mm | 3.0mm | 145 | 2 | | 0  |
| 26032 | Precision Slotted 3.0 (1/8") x 60mm | 3.0mm | 170 | 2.4 | | 0  |
| 26033 | Precision Slotted 3.0 (1/8") x 100mm | 3.0mm | 210 | 3.9 | | 0  |
| 26034 | Precision Slotted 3.0 (1/8") x 150mm | 3.0mm | 260 | 5.9 | | 0  |
| 26035 | Precision Slotted 3.5 (9/64") x 60mm | 3.5mm | 170 | 2.4 | | 0  |
| 26040 | Precision Slotted 4.0 (5/32") x 60mm | 4.0mm | 170 | 2.4 | | 0  |
| 26041 | Precision Slotted 4.0 (5/32") x 100mm | 4.0mm | 210 | 3.9 | | 0  |
| 26042 | Precision Slotted 4.0 (5/32") x 150mm | 4.0mm | 260 | 5.9 | | 0  |

Add to Cart

 Add to Wishlist
  Share on Facebook
  Tweet This
  Pin it

We accept 

Frequently bought together



Price for all selected : [Add selected to cart](#)

This item: [Precision Slotted Screwdrivers](#)



[Pocket Clip For Precision Screwdrivers](#)

[Green Canvas Pouch for Sets](#)

Details

Wiha special chrome-vanadium-molybdenum tool steel
 Through hardened for best wear resistance
 Corrosion protective Vapor Chrome Finish
 Exact fit precision CNC machined tips
 Precision handle is made of high quality cadmium free plastic
 Molded on handle for permanent bond to blade
 The tapered faceted shape allows rapid rotation
 Handles are proportioned to blade size for optimum torque
 Finger tip rotation cap for precise turning and control
 Professional Quality Made In Germany

Additional Info

| | |
|-------------------|--|
| Head Type |   slotted |
| Handle Grip Types | Precision |

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

You may also be interested in the following product(s)



Precision Slotted Screwdrivers 6
Piece Set

Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept



Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge GmbH](#)
[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm
CST USA**

1348 Dundas Cir,
Monticello, MN 55362
Customer Service Email:
cservice@wihatools.com
Tel: 763-295-6591
Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools
In Stock**



Newsletter [Subscribe](#)

