


Home → Tool Types → Screwdrivers → Insulated Slotted Screwdrivers

Insulated Slotted Screwdrivers





Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

★★★★★ 1 Review(s) | [Add Your Review](#)

Filter:

SKU	Product	Size Slotted	Blade Length MM	OAL MM	Blade Length Inch	OAL Inch	Price	Qty
32005	Insulated Slotted Screwdriver 2.0	2.0mm	60	164	3	6.5		0
32010	Insulated Slotted Screwdriver 2.5	2.5mm	75	179	3	7.1		0
32012	Insulated Slotted Screwdriver 3.0	3.0mm	100	204	4	8		0
32015	Insulated Slotted Screwdriver 3.5	3.5mm	100	204	4	8		0
32017	Insulated Slotted Screwdriver 4.0	4.0mm	100	211	4	8.3		0
32023	Insulated Slotted Screwdriver 4.5	4.5mm	100	211	4	8.3		0
32024	Insulated Slotted Screwdriver 4.5	4.5mm	125	236	5	9.3		0
32025	Insulated Slotted Screwdriver 4.5	4.5mm	175	286	7	11.2		0

SKU	Product	Size Slotted	Blade Length MM	OAL MM	Blade Length Inch	OAL Inch	Price	Qty
32026	Insulated Slotted Screwdriver 5.5	5.5mm	175	293	7	11.5		0  
32027	Insulated Slotted Screwdriver 4.5	4.5mm	150	261	6	10.2		0  
32028	Insulated Slotted Screwdriver 4.5	4.5mm	200	311	8	12.3		0  
32031	Insulated Slotted Screwdriver 5.5	5.5mm	125	243	5	9.5		0  
32034	Insulated Slotted Screwdriver 6.0	6.0mm	150	268	6	10.6		0  
32039	Insulated Slotted Screwdriver 6.5	6.5mm	150	268	6	10.6		0  
32042	Insulated Slotted Screwdriver 8.0	8.0mm	175	299	7	11.8		0  
32045	Insulated Slotted Screwdriver 10.0	10.0mm	200	318	8	12.5		0  

Add to Cart

 Add to Wishlist
  Share on Facebook
  Tweet This
  Pin it

We accept 

Details

Meets ASTM F1505, VDE 0682/part201, DIN 7437, EN/IEC 60900, NFPA-70E & CSA specification
 10,000 Volt Tested for a 1,000(AC) 1,500(DC) Volt Certification, VDE and GS tested
 Ergonomic Wiha SoftFinish multi-component handle with roll-off protection
 Cushioned Grip For maximum comfort and power
 Perfect fit for your Hand because of Wiha handle size concept
 Wiha special chrome-vanadium-molybdenum tool steel
 Through hardened for best wear resistance
 Precision machined exact fit Black tips

incredible!! Review by Antonio

Rating ★★★★★

Toughest screwdriver I have ever used!

(Posted on 7/29/2016)

Additional Info

Head Type	⊖ ⊖ slotted
Country of Manufacture	Germany
Handle Grip Types	Insulated

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

[View Full Warranty](#)

You may also be interested in the following product(s)





Insulated
Pliers/Cutters/Screwdrivers 5 Piece
Set

Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)
[Military Discount](#)
[IBEW-NECA Discount](#)
[Filter and sort all Wiha hand tools](#)
[Complete list of tools](#)

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)
[Privacy Policy](#)
[Terms and Conditions](#)
[Having technical issues with the website?](#)

We accept



Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge GmbH](#)
[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm
CST USA**

1348 Dundas Cir,
Monticello, MN 55362
Customer Service Email:
cservice@wihatools.com
Tel: 763-295-6591
Fax: 763-295-6598

[Shipping](#)
[Returns](#)
[Warranty Info](#)
[About Us](#)
[Privacy Policy](#)
[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools
In Stock**



Newsletter [Subscribe](#)