

+ SHIPS FREE
UPS FLAT RATE
MILITARY DISCOUNT
IBEW-NECA DISCOUNT

-  [Home](#)
- [Torx](#)
- [Torque Tools](#)
- [Tech Tools](#)
- [Shop Tools](#)
- [Screwdrivers](#)
- [Pliers](#)
- [Insulated](#)
- [Hex](#)
- [ESD Safe](#)
- [Bits & Sets](#)

[Catalogs](#) [Best Sellers](#) [On Sale](#)

Home → Tool Types → Screwdrivers → Insulated Torx® Screwdrivers

Insulated Torx® Screwdrivers










Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

[Be the first to review this product](#)

Filter:

SKU	Product	Torx Size	Blade Length MM	OAL MM	Blade Length Inch	OAL Inch	Price	Qty
32505	Insulated Torx® Screwdriver T5 x 60mm	T5	60	164	2.4	6.5		<input type="text" value="0"/>  
32511	Insulated Torx® Screwdriver T6 x 60mm	T6	60	164	2.4	6.5		<input type="text" value="0"/>  
32516	Insulated Torx® Screwdriver T7 x 60mm	T7	60	164	2.4	6.5		<input type="text" value="0"/>  
32521	Insulated Torx® Screwdriver T8 x 60mm	T8	60	164	2.4	6.5		<input type="text" value="0"/>  
32526	Insulated Torx® Screwdriver T9 x 60mm	T9	60	164	2.4	6.5		<input type="text" value="0"/>  
32531	Insulated Torx® Screwdriver T10 x 60mm	T10	60	164	2.4	6.5		<input type="text" value="0"/>  
32536	Insulated Torx® Screwdriver T15 x 80mm	T15	80	191	3	7.5		<input type="text" value="0"/>  

SKU	Product	Torx Size	Blade Length MM	OAL MM	Blade Length Inch	OAL Inch	Price	Qty
32541	Insulated Torx® Screwdriver T20 x 80mm	T20	80	191	3	7.5		0  
32546	Insulated Torx® Screwdriver T25 x 80mm	T25	80	198	3	7.5		0  
32551	Insulated Torx® Screwdriver T27 x 100mm	T27	100	218	4	8.6		0  
32556	Insulated Torx® Screwdriver T30 x 100mm	T30	100	218	4	8.6		0  
32561	Insulated Torx® Screwdriver T40 x 150mm	T40	150	274	6	10.8		0  
32566	Insulated Torx® Screwdriver T45 x 150mm	T45	150	274	6	10.8		0  

Add to Cart



 Add to Wishlist
  Share on Facebook
  Tweet This
  Pin it

We accept 

Details

Meets ASTM F1505, VDE 0682/part201, DIN 7437, EN/IEC 60900, NFPA-70E & CSA specification
 10,000 Volt Tested for a 1,000(AC) 1,500(DC) Volt Certification, VDE and GS tested
 Ergonomic Wiha SoftFinish multi-component handle with roll-off protection
 Cushioned Grip For maximum comfort and power
 Perfect fit for your Hand because of Wiha handle size concept
 Wiha special chrome-vanadium-molybdenum tool steel
 Through hardened for best wear resistance
 Precision machined exact fit Black tips
 Torx is a 100% improvement in drive performance over other systems
 Virtually eliminates screw head cam-out

Additional Info

Head Type	  torx
Country of Manufacture	Germany
Handle Grip Types	Insulated

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

[View Full Warranty](#)

You may also be interested in the following product(s)



Insulated Torx® Screwdriver 6 Piece

Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels assure

products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

- [Discounts and promotions](#)
- [Military Discount](#)
- [IBEW-NECA Discount](#)
- [Filter and sort all Wiha hand tools](#)
- [Complete list of tools](#)

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

- [About Us](#)
- [Privacy Policy](#)
- [Terms and Conditions](#)
- [Having technical issues with the website?](#)

We accept



Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge GmbH](#) [Schonach Germany](#)

Monday - Friday Office Hours 7am - 5pm CST USA

1348 Dundas Cir,
Monticello, MN 55362
Customer Service Email:
cservice@wihatools.com
Tel: 763-295-6591
Fax: 763-295-6598

- [Shipping](#)
- [Returns](#)
- [Warranty Info](#)
- [About Us](#)
- [Privacy Policy](#)
- [Terms and Conditions](#)

Over 5000 Professional Quality Wiha Tools In Stock



Newsletter [Subscribe](#)