

Home -> Insulated -> Insulated Multi Tool Sets -> Insulated Pliers/Screwdrivers 50 Piece Set

Insulated Pliers/Screwdrivers 50 Piece Set



Zoom

Be the first to review this product

Insulated Tool Set with Pliers, Cutters, Nut Drivers, Screwdrivers, T Handles, Knife & Ruler. 50 Piece Set in Tool Box

SKU: 32874

Add to Cart

Qty: 1

Add to Wishlist Share on Facebook Tweet This Pin it

We accept amazon pay

Details

Tools in Canvas Tool Bag
Insulated 10,000 Volt Tested, 1000 Volt Rated
Tools Comply with one or more of the following standards: VDE, ASTM, IEC, CSA, OSHA, EN/IEC, NFPA.

Additional Info

SKU	32874
Weight (lbs)	19.3000

High Visibility Ergonomic Soft Comfort Grips on Handles.
All Tools Individually tested for maximum safety performance

Screwdrivers

- > Slotted 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.5, 6.0, 6.5, 8.0mm
- > Phillips #0, 1, 2, 3
- > Square #1 & 2
- > Xeno #1 & 2
- > Torx T8, T9, T10, T15, T20, T25, T27, T30

T Handles

- > Hex Inch 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"

Inch Nut Drivers







- > 7/32, 1/4, 5/16, 3/8, 7/16, 1/2"

Pliers Included

- > 6.3" & 8" Long Nose Pliers
- > 6.3" Combo Pliers
- > 9" Combo Pliers/Crimpers
- > 6.3" side Cutters
- > 8" BiCut SuperCut
- > 6.3" Stripping Pliers
- > 8" Adjustable Wrench
- > 10" Water Pump Pliers

Accessories

- > 50mm insulated cable stripping knife
- > 2 Meter In/MM folding ruler
- > Battery operated voltage detector

Country of Manufacture	Germany
Pieces In Set	50
 Phillips Sizes	#0 #1 #2 #3
 Slotted Sizes	2.0mm~5/64" 2.5mm ~3/32" 3.0mm~1/8" 3.5mm~9/64" 4.0mm~5/32" 4.5mm~11/64" 5.5mm~7/32" 6.0mm~15/64" 6.5mm~1/4" 8.0mm~5/16"
 Hex Inch Sizes	5/32" 3/16" 7/32" 1/4" 5/16" 3/8"
 Torx Sizes	T8 T9 T10 T15 T20 T25 T27 T30
 Square Sizes	1, 2
Inch Nut Driver Sizes	7/32" 1/4" 5/16" 3/8" 7/16" 1/2"
 Terminal Block / Xeno Sizes	#1, #2

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

[View Full Warranty](#)

Customers Also Bought





Wiha Hat

Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

Discounts and promotions

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.


[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept



Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge Gmbh](#)
[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm
CST USA**

1348 Dundas Cir,

Monticello, MN 55362

Customer Service Email:

cservice@wihatools.com

Tel: 763-295-6591

Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools
In Stock**



Newsletter

[Subscribe](#)

