

Home -> Screwdrivers -> Precision Screwdrivers -> Master Technicians Bench Top 50 Piece Precision Screwdriver Set

Master Technicians Bench Top 50 Piece Precision Screwdriver Set



Zoom

Be the first to review this product

Master Technicians Bench Top Set 50 Piece in Rack

SKU: 92190

Add to Cart

Qty: 1

Add to Wishlist Share on Facebook Tweet This Pin it

We accept amazon pay

Details






Sizes:
Slotted: 0.8, 1.0, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5 4.0mm
Phillips: #000, #00, #0, #1
Hex: 0.7~0.028", 0.9~0.035", 1.3~0.050", 1.5, 2.0, 2.5, 3.0mm, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32
Torx: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
Nut Drivers: 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm

Additional Info

SKU	92190
Weight (lbs)	3.6700
Head Type	slotted, phillips, hex metric, hex inch, torx, nut driver metric, chip lifter

Chip Lifter
 Wiha special chrome-vanadium-molybdenum tool steel
 Through hardened for best wear resistance
 Corrosion protective Hard Chrome Finish
 Exact Fit Precision Machined Tips
 Precision Handle is made of high Quality cadmium free Plastic
 Molded on handle for permanent bond to blade
 The Tapered Shape allows rapid rotation
 Handles Proportioned to Blade Size for optimum torque
 Precision Turning and Control with the Rotating Cap

Comes with High Quality Metall Stand

Country of Manufacture	Germany
Handle Grip Types	Precision
 Phillips Sizes	#000 #00 #0 #1
 Slotted Sizes	.80mm~1/32" 1.0mm~1/32" 1.2mm~3/64" 1.5mm~1/16" 1.8mm~1/16" 2.0mm~5/64" 2.5mm ~3/32" 3.0mm~1/8" 3.5mm~9/64" 4.0mm~5/32"
 Hex Metric Sizes	1.3mm 1.5mm 2.0mm 2.5mm 3.0mm
 Hex Inch Sizes	0.028" ~ 0.7mm 0.035" ~ 0.9mm 0.050" ~ 1.3mm 1/16" 5/64" 3/32" 7/64" 1/8" 9/64" 5/32"
 Torx Sizes	T1 T2 T3 T4 T5 T6 T7 T8 T9 T10
Pieces In Set	50

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

[View Full Warranty](#)

Customers Also Bought





Wiha Hat

Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept



Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge Gmbh](#)
[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm
CST USA**

1348 Dundas Cir,
Monticello, MN 55362
Customer Service Email:
cservice@wihatools.com
Tel: 763-295-6591
Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools
In Stock**



Newsletter [Subscribe](#)

