

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370008](#)
Status: **Active**
Overview: Outlet Boxes
Description: Super-Safeway® Multiple Outlet Box, Extended Depth, 2-Sided, Cord Clamp, with Cover Plates for (2) Single Straight-Blade Receptacles

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E46237

General

Product Family Power Distribution
 Series [130137](#)
 Enclosure Rating NEMA 4
 GFCI Reset N/A
 Mounting Style Portable
 Open Neutral Relay N/A
 Overview [Outlet Boxes](#)
 Product Literature Order No 987650-7737
 Product Name Super-Safeway™
 Receptacle Type Single
 Type Multiple Outlet Box
 UPC 78678875041
 Woodhead Yes

Physical

Cord Diameter 8.26-16.64mm (.325-.655")
 Cord Grip Body Size F3 3/4"
 Cord Length N/A
 Feed-Thru No
 Flip Lid Yes
 Material - Housing Rubber
 Number of Receptacles 1 - Customer Supplied
 Packaging Type Carton

Electrical

Cord Type N/A
 Current - Maximum per Contact Per Cust. Supplied Receptacle
 GFCI No
 Ground Continuity Monitor No
 NEMA Configuration NEMA L5-20
 Voltage - Maximum Per Cust. Supplied Receptacle

Material Info

Engineering Number 3081



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130137](#) Series