

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130153-0114](#)
Status: **Active**
Overview: Ground Fault Circuit Interrupter (GFCI) Products
Description: Super-Safeway® In-Line Industrial GFCI, Portable, Single Phase, Automatic Reset, Molded NEMA L5-20, 20A, 120V, 0.61m (2.0') Cord Length

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)
[Product Literature \(PDF\)](#)

Agency Certification

UL E66308

General

Product Family Power Distribution
Series [130153](#)
Enclosure Rating NEMA 4X
GFCI Reset Automatic
Mounting Style Portable
Open Neutral Relay Yes
Overview [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
Product Literature Order No 987650-7737, 987651-0452
Product Name Super-Safeway™
Receptacle Type N/A
Type GFCI Industrial Duty, Single Phase
UPC 78678888275
Woodhead Yes

Physical

Cord Diameter 10.67mm (.420")
Cord Grip Body Size Internal Double C-Clamp
Cord Length 0.61m (2.0')
Feed-Thru Yes
Flip Lid No
Material - Housing Nylon
Net Weight 999.990/kg
Number of Receptacles 1
Packaging Type Bag

Electrical

Cord Type 12/3 SJEOOW
Current - Maximum per Contact 20A
GFCI Yes-In-line
Ground Continuity Monitor No
NEMA Configuration NEMA L5-20
Voltage - Maximum N/A

Material Info

Old Part Number 20051-1MLDA



EU RoHS China RoHS

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130153Series](#)