

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130083-0264](#)
Status: **Active**
Overview: Electric Reels
Description: Woodhead® POW-R-MITE® Industrial Duty Cable Reel, 12/3 SOW, 7.62m (25.0') Cord Length

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR29921
 UL E22769

General

Product Family Electric Reels
 Series [130083](#)
 Cable Length N/A
 Comments Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.
 Depth 0.34m (13.50")
 Duty Industrial
 Enclosure Rating NEMA 4
 Height 0.37m (14.50")
 NEMA Configuration N/A
 Overview [Electric Reels](#)
 Product Literature Order No 987650-8062
 Product Name POW-R-MITE®
 Type Cable Reel
 UPC 78678879383
 Width 244.35mm (9.620")
 Woodhead Yes

Physical

Cable Movement Ratchet Lock
 Cord Length 7.62m (25.0')
 Drum Lock Ratchet
 Guide Arm 5° increments over 270° Arc
 Material - Coating Powder Coating
 Material - Housing Cast Aluminum
 Mounting Style Rigid
 Number of Conductors 3
 Packaging Type Carton
 Primary Cord/Cable Entry 1" NPT
 Retraction Weight 1.8kg (4.0 lb)
 Wire Size AWG 12

Electrical

Bulb Included N/A
 Cord Type 12/3 SOW
 Current - Maximum per Contact 18A
 GFCI No
 Lamp Type N/A
 Lamp Wattage - Maximum N/A
 On/Off Switch N/A
 Voltage - Maximum 600V



EU RoHS

Not RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130083Series

Material Info

Old Part Number

9383

Reference - Drawing Numbers

Sales Drawing

SD-130083-035

This document was generated on 10/06/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION