

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1210350133](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: Micro-Change (M12) to Brad mPm DIN Form A - 18mm Cordset, 5 Poles, Male (Straight) to Male (90°), 0.60m (1.97') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|--------------------|--|
| Product Family | Industrial Cordsets |
| Series | 121035 |
| Connector End A | Brad mPm DIN A - 18mm |
| Connector End B | Micro-Change (M12) |
| IP Rating | IP65 |
| Material - Contact | Copper Alloy |
| Overview | mPm DIN Valve Connectors |
| Product Name | Micro-Change (M12), mPm |
| Protocol | N/A |
| Region | America, Europe |
| Type | Double Ended |
| UPC | 883906334703 |

Physical

| | |
|-------------------------------|---------------------|
| Cable Diameter | 5.72mm (.225") |
| Cable Length | 0.60m (1.97') |
| Color - Cable Jacket | Black |
| Coupling Style | Threaded |
| Gender | Male-Male |
| Keyway | Single |
| LED Indicator | No |
| Material - Cable Jacket | PUR |
| Material - Connector Body | Polypropylene |
| Material - Coupling Nut | Nickel-plated Brass |
| Material - Plating Mating | Gold over Nickel |
| Net Weight | 62.490/g |
| Orientation | 90° to Straight |
| Poles | 5 |
| Temperature Range - Operating | -25°C to +75°C |
| Wire Size AWG | 22 |
| Wire/Cable Type | Shielded PUR |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 1.5A |
| Voltage - Maximum | N/A |

Material Info

| | |
|--------------------|---------------|
| Engineering Number | E85000P12M006 |
|--------------------|---------------|

Reference - Drawing Numbers

| | |
|---------------|---------------|
| Sales Drawing | SD-121036-001 |
|---------------|---------------|

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - ED/71/2019 (16 July 2019)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[121035](#) Series