

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130057-0003](#)
Status: **Active**
Overview: [industrial ethernet solutions](#)
Description: Brad® RJ-Lnxx™, Threaded, RJ-45 Ethernet Field-Attachable Connector for Solid Core Cable

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	130057
IP Rating	IP67
Overview	industrial ethernet solutions
Product Name	Brad®, RJ-Lnxx®
Type	Field Attachable Connector
UPC	78678842476

Physical

Cable Diameter	N/A
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	None
Material - Connector Body	Polycarbonate
Material - Contact	Copper
Material - Coupling Nut	ABS
Material - Plating Mating	n/a
Net Weight	21.290/g
Orientation	Straight
Poles	N/A
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	4A
Voltage - Maximum	125V DC

Material Info

Old Part Number	ENSAM315
-----------------	----------

Reference - Drawing Numbers

Sales Drawing	SD-130057-002
---------------	---------------




image - Reference only

EU RoHS

RoHS Compliant by Exemption

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130057Series