

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300190023](#)
Status: **Active**
Description: Die Block 4 Pole Cast Receptacle, Orange

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E46237

General

Product Family Industrial Receptacles
 Series [130019](#)
 IP Rating N/A
 Product Name Die Block
 Type Die Block
 UPC 78678843305

Physical

Coupling Type Push to Lock
 Gender Female
 Keyway N/A
 Length N/A
 Material - Component Nickel-plated Brass
 Mounting Thread Size N/A
 Net Weight 99.000/g
 Orientation N/A
 Panel Mount Back, Front
 Poles 4
 Temperature Range - Operating N/A
 Wire Size AWG N/A
 Wire/Cable Type N/A

Electrical

Current - Maximum per Contact 25.0A
 Voltage - Maximum 600V AC

Material Info

Engineering Number 43305

Reference - Drawing Numbers

Sales Drawing SD-130019-005



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130019 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION