

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300350085](#)
Status: **Active**
Overview: [DeviceNet Solutions](#)
Description: DeviceNet Mini-Change Tee, 4 Poles, Female/Male with Female Drop

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Industrial Tees and Splitters
 Series [130035](#)
 IP Rating IP67
 Overview [DeviceNet Solutions](#)
 Product Name DeviceNet Trunk
 Type Power Tap Tee
 UPC 78678850378

Physical

Drop Connector Mini-Change
 Drop Gender Female
 Keyway Single
 LED Indicator No
 Left Trunk Connector Mini-Change
 Left Trunk Gender Female
 Leg 1 Length N/A
 Leg 2 Length N/A
 Material - Cable Jacket N/A
 Material - Connector Body TPE
 Material - Coupling Nut Black Epoxy Coated Zinc
 Net Weight 91.625/g
 Poles 4
 Right Trunk Connector Mini-Change
 Right Trunk Gender Male
 Temperature Range - Operating -20°C to +80°C

Electrical


Current - Maximum per Contact 10.0A
 Voltage - Maximum 600V DC

Material Info

Engineering Number DNETAUXPT

Reference - Drawing Numbers

Sales Drawing SD-130035-014



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[130035 Series](#)