

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300910059](#)
Status: **Active**
Overview: Reels - Woodhead
Description: Woodhead Standard Cord Reel, 14/3 SJTOW Cord, 13.72m (45.0') Cord Length with 15A GFCI Pendant Outlet Box, One Duplex, NEMA 5-15 Outlet

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

General

Product Family	Electric Reels
Series	130091
Cable Length	0.457m (1.50')
Depth	0.30m (11.75")
Duty	Standard
Enclosure Rating	NEMA 1
Exclude SD Check	Yes
Height	0.36m (14.25")
NEMA Configuration	NEMA 5-15
Overview	<u>Reels - Woodhead</u>
Product Literature Order No	987650-8061
Product Name	Super-Safeway
Type	Cord Reel
UPC	78678833625
Width	196.85mm (7.750")

Physical

Cable Movement	Ratchet Lock
Cord Length	13.72m (45.0')
Drum Lock	Ratchet
Guide Arm	2 - Position
Material - Coating	Powder Coating
Material - Housing	Steel/Polycarbonate
Mounting Style	Rigid
Number of Conductors	3
Number of Receptacles	2
Packaging Type	Carton
Primary Cord/Cable Entry	N/A
Retraction Weight	1.4kg (3.0 lb)
Wire Size AWG	14

Electrical

Bulb Included	N/A
Cord Type	14/3 SJTOW
Current - Maximum per Contact	11.0A
GFCI	Yes
Lamp Type	N/A
Lamp Wattage - Maximum	N/A
On/Off Switch	No
Voltage - Maximum	120V

Material Info

Engineering Number	990-3070G
--------------------	-----------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130091](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION