

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300910201](#)

Status: **Active**

Overview: [Reels - Woodhead](#)

Description: Woodhead Standard Duty Cord Reel, 12/3 SJTOW Cord, 10.67m (35.0') Cord Length, NEMA 5-20 Straight Blade Plug, with 20A NEMA 5-20 Straight Blade Outlet Box, Dual-Sided Duplex

Documents:

[Drawing \(PDF\)](#)

[Product Literature \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR29921

General

Product Family	Electric Reels
Series	130091
Cable Length	0.61m (2.0')
Depth	0.30m (11.75")
Duty	Standard
Enclosure Rating	NEMA 1
Exclude SD Check	Yes
Height	0.36m (14.25")
NEMA Configuration	NEMA 5-20
Overview	Reels - Woodhead
Product Literature Order No	987651-4611
Product Name	Super-Safeway
Type	Cord Reel
UPC	78172548542
Width	196.85mm (7.750")

Physical

Cable Movement	Ratchet Lock
Cord Length	10.67m (35.0')
Drum Lock	Ratchet
Guide Arm	2 - Position
Material - Coating	Powder Coating
Material - Housing	Steel/Polycarbonate
Mounting Style	Rigid
Net Weight	26761.928/g
Number of Conductors	3
Number of Receptacles	4
Packaging Type	Carton
Primary Cord/Cable Entry	N/A
Retraction Weight	1.4kg (3.0 lb)
Wire Size AWG	12

Electrical

Bulb Included	N/A
Cord Type	12/3 SJTOW
Current - Maximum per Contact	20.0A
GFCI	No
Lamp Type	N/A
Lamp Wattage - Maximum	N/A
On/Off Switch	No
Voltage - Maximum	120V

Material Info



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130091](#) Series

Engineering Number

998-3080

Reference - Drawing Numbers

Sales Drawing

SD-130091-011

This document was generated on 03/26/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION