

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300980048](#)
Status: **Active**
Overview: Strain-Relief Cord Grips
Description: MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, Straight Male, Cable Diameter 4.75-6.35mm (.187-.250"), Stainless Steel

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

General


Product Family	Cable Grips
Series	130098
Exclude SD Check	Yes
Eye Type	N/A
NEMA Rating	NEMA 3R
O-Ring	No
Overview	Strain-Relief Cord Grips
Product Literature Order No	987651-6081
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678835117
Use With	1/2" NPT MAX-LOC Lock Nut 1300990143 , MAX-LOC O-Ring, 1/2" NPT 1301800314 , 1/2" NPT MAX-LOC Gasket 1300990149

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	4.75-6.35mm (.187-.250")
Color - Grommet	Orange
Gender	Male
Material - Body	Stainless Steel
Material - Grip	Stainless Steel
Mesh Length	N/A
Number of Holes	1
Thread Size	1/2" NPT

Material Info

Engineering Number	5522SS
--------------------	--------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130098](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION