

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300980095](#)
Status: **Active**
Overview: [Strain-Relief Cord Grips](#)
Description: MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, 90° Angle Male with O-Ring, Cable Diameter 14.27-15.88mm (.562-.625")

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR32159
 UL E76954

General

Product Family Cable Grips
 Series [130098](#)
 Exclude SD Check Yes
 Eye Type N/A
 NEMA Rating NEMA 6P
 O-Ring Yes
 Overview [Strain-Relief Cord Grips](#)
 Product Literature Order No 987651-6081
 Product Name MAX-LOC
 Type Strain Relief Grip
 UPC 78678855352
 Use With 3/4" NPT MAX-LOC Lock Nut [1300990144](#)

Physical

Approximate Break Strength N/A
 Bale Length N/A
 Body Style 90° Angle
 Cable Diameter 14.27-15.88mm (.562-.625")
 Color - Grommet N/A
 Gender Male
 Material - Body Nylon
 Material - Grip N/A
 Mesh Length N/A
 Number of Holes 1
 Thread Size 3/4" NPT

Material Info

Engineering Number 5535W



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130098 Series](#)